


4032, 4033, 4034, 4035 Progressive Movement Full Extension Rail Disconnect Applications: File drawers in desks, credenzas, and lateral files. Also store fixtures, hotel, or institutional furniture. Vertical drawer adjustment with rail cam. This product is covered by U.S. and various foreign patents issued and/or pending.

4032 / 4033 / 4034 / 4035 QUICK REFERENCE

Side Space: 1/2" + 1/32" x 2 Slide Lenghts: 12"–28" Overall slide dimensions 3.79" x 1/2" Load Rating:100–150 lbs.



Finishes:	Bright electro-zinc (C) or black zinc (CB) plating available
Lengths:	12"–28" [300 mm–700 mm]
Height:	3.19" (3.79" including rail) [81.0 mm (96.3 mm including rail)]

- Travel: See Chart
- Movement: See Chart
 - Load: Models 4032/4034: 150 lb.** [68 kg.] Models 4033/4035: 100 lb.** [45 kg.]

Part	Actual	Tra	Α	в	С	
Number	Length	4032/4033	4034/4035		_	-
403X-12	11.81	12.27	13.27			
4037-12	[300]	[312]	[337]			
403X-14	13.78	14.21	15.21			
	[350]	[361]	[386]			
403X-16	15.75	16.15	17.65	12.60		
4038-16	[400]	[410]	[448]	[320.0]		
403X-18	17.72	18.10	19.60	13.86		
4037-10	[450]	[460]	[498]	[352.0]		
403X-20	19.69	20.03	21.53	16.38		
403X-20	[500]	[509]	[547]	[416.0]		
403X-22	21.65	21.95	23.45	13.86	17.64	18.90
	[550]	[558]	[596]	[352.0]	[448.0]	[480.0]
403X-24	23.62	24.39	25.39	13.86	18.90	
	[600]	[620]	[645]	[352.0]	[480.0]	
403X-26	25.59	26.33	27.33	13.86	21.42	
	[650]	[669]	[694]	[352.0]	[544.0]	
1022 20	27.56	28.27	29.27	13.86	21.42	23.94
403X-28	[700]	[718]	[743]	[352.0]	[544.0]	[608.0]

Sidespace:	1/2" +1/32", -0.0 [(.50" +.03", -0.0) 12.7 mm (+0.8 mm, -0.0)]
Hardware:	Flathead 6 mm Euro screws or #8 pan head screws
Mounting :	Side mount only; 32 mm or traditional hole pattern
Disconnect:	Rail lift off (See Chart)

Features: Progressive movement, positive stop, silenced in and out, handed, detent in

Model	Travel	Ball Bearings	Max. Drawer Width		er	Previous Model		
4032	Full	Steel	27" [686 mm]		ןו	437, 4025		
4033 Full		Polymer	er 18" [450 mm]		ןו	4037		
4034	Over	Steel	24" [600 mm]		ןו	417, 432, 4005		
4035	Over	Polymer	18" [450 mm]		4017			
	Rail Part Numbers		e	Rail Length		Е	F	
7156-1214-XL 7156-1214-XR		12"–14" [300-350]		10.54 [267.7]		4.00 101.6]	7.56 [192.0]	
7156-1518-XL 7156-1518-XR		15"–18" [381-450]		13.06 [331.7]		4.00 101.6]	10.08 [256.0]	
7156-1921-XL 7156-1921-XR		19"–21" [483-533]		16.84 [427.7]	4.00 [101.6]		13.86 [352.0]	
7156-2225-XL 7156-2225-XR		22"–25" [550–635]		20.62 [523.8]		7.00 177.8]	17.64 [448.1]	
7156-2628-XL 7156-2628-XR		26"–28" [650–700]	24.40 [619.8]		7.00 177.8]	21.42 [544.1]	

"X" = "C" for zinc finish; or "B" for black finish

** Models 4032/4034: 18" slide cycled 75,000 times. Models 4033/4035: 18" slide cycled 50,000 times.

Installation Instructions


Conventional Mounting Cabinet Member Installation

- 1. Mark a horizontal line in the cabinet sidewall 1 ½" (11/16" min.) up from the cabinet floor to the center line of the cabinet member. Mark a point on the line 2-3/8" in from the cabinet front. This will position the slide flush with the cabinet opening. For inset drawers, add the drawer front thickness to this dimension. See Figure 1.
- 2. Measure the distance between the front and rear horizontal slots on the slide. Mark this measurement on the horizontal line beginning at the first mark.
- 3. Make a pilot hole on each mark, either with an awl or 1/8" drill. Install #8 screws through the front and rear horizontal slots.


Rail Installation

- 1. Mark a horizontal line on the drawer side 2-27/32" above the center line of the cabinet member. See Figure 3.
- Mark a point on this line 5/8" back from the drawer front. Install #8 screw through the cam adjuster and through a slot at the rear. See Figure 3.

NOTE: The cam screw must install on the same center line as the remaining rail mounting screws. This eliminates additional measuring and marking.



3. Connect the drawer to the extended slide members by lowering the drawer onto the slides so the rail lock arm rests on top of the slide members approximately 1" from the front. Pull both slides forward until the rail latch locks securely into each slide.



4. Rotate the cam with a Phillips or Pozi screwdriver to vertically position the drawer in relation to the cabinet.



5. **IMPORTANT:** After all adjustments are made, secure rail with additional mounting screws.

32 mm System Mounting

Cabinet Member Installation

 Install an M-6 euro screw through the second hole from the front of the slide and into a 5 mm hole located 37 mm in from the front of the cabinet. Select a rear mounting hole on one of the 32 mm multiples provided and install screws. See Figure 2.

Rail Installation


- 1. Mark a horizontal line on the drawer side 72.4 mm above the slide center line. See Figure 3.
- Mark a point on this line 15.9 mm back from the drawer front. Complete rail installation by following steps 3 through 5 above.

Packaging Information

Distributor (D) Pack: Polybag includes one pair of slides, rails, and screws. All lengths packaged 5 pair per box.

Bulk Pack: Slides and rails are packed in separate boxes. Lengths 12"–18", 20 each/box. Lengths 20"–28", 10 each/box.

X-Pack (X): Slides, rails, and screws are packed in one box. All models available. All lengths packaged 5 pair per box.



Slide/Rail Ordering Instructions

Complete your slide order for models 4032, 4033, 4034, 4035 by specifying the total slides required, slide finish, slide model, slide length, and optional polybag packaging.

Example: 10 Each C 4034-12 D

Complete your rail order by specifying quantity, rail part number, rail finish ("C" for zinc; "B" for black) and hand ("L" for left hand; "R" for right hand).

Example: 10 Each 7156-1214-CL (zinc/left hand) 10 Each 7156-1214-BR (black/right hand)

Specifications

Slide members and ball retainers: Cold rolled steel Ball bearings: Models 4032 & 4034: Carburized steel Models 4033 & 4035: Acetal polymer

RoHs compliant **Note:** Specifications, materials, prices, terms, and delivery are subject to change without notice.

accuride

ACCURIDE INTERNATIONAL INC.

12311 Shoemaker Avenue Santa Fe Springs, CA 90670 TEL (562) 903-0200 FAX (562) 903-0208 www.accuride.com Manufacturing, Engineering, and Sales United States • Germany • Japan • Mex

United States • Germany • Japan • Mexico • United Kingdom • China

Copyright © 2002 Accuride International Inc. 3700-9309(9082)-MK039-R11-0116